





**FEEL UNIQUE 01** Pattern Fruits 36 - 41



**FEEL UNIQUE 04** Pattern Tropical 36 - 41



**FEEL UNIQUE 05** Pattern Heartbeat 36 – 41



**FEEL UNIQUE 06** Pattern Fork 36 - 41



The **FEEL UNIQUE** clog offers you the benefits of light and comfortable footwear, from early morning until the end of your day. All this with the greatest freedom of expression, through various standards you affirm your uniqueness.

## Description

**FEEL UNIQUE**, is a clog produced entirely from polymeric materials and microfibers and has the following components:

- Antistatic device;
- Heel-strap.

### Users

FEEL UNIQUE, is ideal for uses where prolonged standing or walking may tend to induce foot discomfort or lower body fatigue, especially to be used in:



Hospitals and Other Healthcare Institutions



Catering industry



**Beauty & Cosmetic** Institutes



Everyone with

## **Specifications**



### **Super Light**

Feelite™ technology produces remarkably light, resistant and comfortable footwear.



## **Shock Absorption**

The special design helps to reduce the occurrence of micro-lesions in tendons, bones and joints, and the feeling of tired legs.



The footwear can be machine washed up to 30°C.



## **Upper Liquid Protection**

Avoids the entrance of liquids inside the shoe.



## Removable Insole

It's detachable to allow a deeper cleaning.



## **Breathable**

Regulates the temperature and humidity of the foot.



## Antislip

The sole is designed to reduce the risk of slipping.



## Promotes the dissipation of accumulated static electricity.



# Style designed to be worn by men and women.

**Materials and Technologies** 



FEEL UNIQUE is made with Feelite™ technology. This technology is super lightweight and provides extreme comfort.

## **Technical Specifications**

- · Machine washing up to a maximum of 30 °C;
- Slip-resistant;
- Resistant to abrasion.



## **Technical Standard**



Regulation 2016/425.

Chemical resistance Indicatives Material: FEELITE®		Chemical resistance Indicatives Material: FEELITE®	
Medium	EVA Grades	Medium	EVA Grades
AQUEOUS		OXYGENATED SOLVENT	
DEIONIZED WATER	1	ACETONE	2
HYDROCHLORIC ACID, 10%	2	DI-ETHYLENE GLYCOL	2
NITRIC ACID, 10%	2	ETHYL ACETATE	2
NITRIC ACID, 40%	3	ETHYL ALCOHOL	2
NITRIC ACID, 50%	3	ETHLENE GLYCOL	2
SODIUM HYDROXIDE, 50%	3	ETHANOL	1
SULFURIC ACID, 10%	3	METHYL ETHYL KETONE	2
SULFURIC ACID, 30%	3	METHYL ISOBUTYL KETONE	2
HYDROCARBONS	-	PROPANOL OTHERS	1
ASTM 3 OIL	2	ACETIC ACID	1
DIESEL	3	CHLOROFORM	2
GASOLINE	3		
HEXANE	3		
MINERAL OIL	3		
TOLUENE	3		

Legend: 1 = Excelent; 2 = Good; 3 = Limited; 4 = Not recommended

## **Care and Cleaning**

Wash: Machine washable up to a maximum temperature of 30°C. The removable insole must be washed inside the clog.

Dry: Wipe with a cloth or dry at room temperature, without direct exposure to light.

## Attention

FEEL UNIQUE resists several washings at 30°C in washing machine. It is not recommended the use of bleaching agents during washing machine

To keep your shoes new and beautiful for much longer, it is essential to follow some recommendations: Avoid getting your shoes wet, but in case this occurs, never place them in the sun. Let them dry in the shade and also away from any other source of heat, because heat damages the materials, the colour and the texture. A soft cloth is the main ally of this type of shoe and its cleaning should be done weekly or whenever necessary.





## **DECLARATION OF CONFORMITY**

MANUFACTURER: WALKEMORE S.A

Rua das casas queimadas 567 4415-439 VN Gaia, Portugal

This EU declaration of conformity is issued under the sole responsibility of the manufacturer, who declares that the equipment included by this declaration complies with Regulation (EU) 2016/425 for Personal Protective Equipment - Category I.

PRODUCT NAME: FEEL UNIQUE



FEEL UNIQUE 01 - Kitchen Designs FEEL UNIQUE 04 - Flowers Designs



FEEL UNIQUE 05 - Medical Designs FEEL UNIQUE 08 - Horeca design

**PRODUCT DESCRIPTION:** Clogs from WOCK® brand, with soles, microfibre and lycra upper, with removable

PU insoles.

NOTIFIED BODY: Not applicable

**CONFORMITY ACESSMENT:** In accordance with the procedure described in Module A of Regulation

(EU) No 2016/425

TECHNICAL CHARACTERISTICS: Specific ergonomics features: EN ISO 20347:2012/5.3.3 / EN ISO 20344:2011/5.1

Thickness of upper: EN ISO 20347:2012/5.4.2 / EN ISO 20344:2011/6.1 Tensile properties of upper: EN ISO 20347:2012/5.4.4 / EN ISO 20344:2011/6.4 Flexing resistance of upper: EN ISO 20347:2012/5.4.5 / EN ISO 20344:2011/6.5 Tear strength of outsole: EN ISO 20347:2012/5.8.2 / EN ISO 20344:2011/8.2 Abrasion resistance of outsole: EN ISO 20347:2012/5.8.3 / EN ISO 20344:2011/8.3 Flexing resistance of outsole: EN ISO 20347:2012/5.8.4 / EN ISO 20344:2011/8.4 Antistatic

footwear: EN ISO 20347:2012/6.2.2.2 / EN ISO 20344:2011/5.10

Energy absorption of seat region: EN ISO 20347:2012 / 6.2.4 / EN ISO

20344:2011/5.14

**ADDITIONAL INFORMATION:** Washability at 30°C: Based on

Insole cannot be washed or sterilized in an autoclave.

Grijó, 02 January 2024



